

## Ceiling/Wall Pull Unit

Part No. **QT607**



### Overview

- Can be used to generate a Standard or Ensuite call on a Quantec Addressable Call System.
- Ceiling or wall mountable.
- Typically wired as a slave to a Quantec Addressable Call Point or Quantec Accessible Toilet Reset Point.
- Supplied with 3m of red nylon pull cord and two red open-sided triangular bangles for ease of use by the infirm.
- Red confidence LED and diffuser emits a bright red glow over a wide area to reassure the user that a call has been made.
- Surface mountable.
- Base fits 16mm conduit and BESA centres.
- Also available as part of the QT951 Accessible Toilet Expansion Kit.



### More Information

### Technical Specifications

Quiescent current	Less than 3mA.
Alarm current	6mA.
Indicators	Red reassurance LED/diffuser (active in Alarm).
Controls	Red pull cord (activated by pulling one of the QT607's bangles).
Connections	Local +V; S (Switch); R (Red). Wire as a slave to a Quantec Addressable Call Point or Accessible Toilet Reset Point. See instructions for details.
Onboard Sounder	No,
Product dimensions (mm)	93mm diameter x 27mm deep. Designed for ceiling/wall mounting only. Base fits 16mm conduit and BESA centres.
Construction & finish	Plastic.



IP Rating IP21.  
Weight 56g.  
Operating conditions/temperature -5°C to +40°C. Max. relative humidity 95% non-condensing.



T 01942 322744 E [sales@c-tec.co.uk](mailto:sales@c-tec.co.uk)  
F 01942 829867 W [www.c-tec.com](http://www.c-tec.com)



C-TEC, Challenge Way, Martland Park, Wigan, WN5 0LD United Kingdom